

DESCRIPTION

The creation of this bass trap patent and its manufacturing method consists of a very solid metal box, on which a bitumen elastic layer on each of the two sides is applied. The resonator's absorbing surfaces are thin massive plates: the front one with high elasticity and low internal friction and the back plate with less elasticity causing a high internal friction. This combination creates an all-over solid connection through the metal box between the front and back plates. This compound forms a box sealed all around, closed to the air pressure, but opened to the sound. The front and the back plates do not prevent the entering of low frequencies from going inside the box interacting with a different air pressure. Like a tunable Helmholtz resonator, the membrane is excited by the resonance frequency and it vibrates so strong that the weight of the limp mass pushes and pulls the air cushion inside the hox

The ABSTRACT® resonance box formula comprises two limp elastic masses separated by the distance between them, benefiting the isothermal compression, thus providing better sensibility by absorbing the low-end frequencies at very low sound pressure levels. This system is very sensitive, however, the louder the sound system is, pumping the volume up, the more absorption you can get. Consequently it is an incredible high-efficiency low-frequency absorber panel.

By using a simple air compressor device you are free to vary and change the internal air pressure, hence obtaining various different frequencies of absorption. The distance between the membranes

FEATURES

αS

αS

1.0 0.8 0.6

0.4 0.2

Hz

αS

- Uses 60% of recycled materials and 100% recyclable.
- Fire-resistance: Euroclass B (similar to old M1).
- Variable tuned: 80Hz, 100Hz or 125Hz [>50Hz;<250Hz].
- · Peak absorption at Low Frequency: nominal pressure = 0.85 / 80Hz
- 8 mBar = 0.86 / 100Hz 14 mBar = 0.88 / 125Hz
- Package and Installation: individual and accessories included.
- · Ideal for mid and large size halls

ABSORPTION COEFFICIENT

varies according to the internal air pressure difference; for example with positive air pressurization we have a bigger distance and the air pressure superior to the original exterior pressure. As result, the frequency varies in accordance with the mentioned frequencies pattern.

In a more or less intense way, the problem of the low-frequencies control is widespread in most room types; This model is ideal for Concert venues, Auditoriums, Pavilions, studios, music rooms; these are the type of rooms that can greatly benefit from the integration of these acoustic modules, once they are the most effective and accurate way to intervene in solving the problems of low-frequencies.

MODELS AND SIZES

MODELS	HEIGHT	WIDTH	DEPTH	WEIGHT
BSW 200	200 cm	100 cm	20 cm	45 Kg
BSW 100	100 cm	100 cm	20 cm	24 Kg

TECHNICAL DRAWINGS





ABSORPTION COEFFICIENT: Values in accordance with the standards: EN 20654, ASTM C423 and EN 11654.

Values [<100Hz and > 5K] are Non Standard Values.

STANDARD FABRIC COLOURS



IMPORTANT NOTICES

JOCAVI[®] accepts no responsibility for any printing errors. Specifications can be modified without prior notice, if technical or commercial reasons so require.
RAL[®] is an international independent colour standard system partner for industry, trade, architecture and design. Should be consulted before placing any order.
RAL[®] is an international independent colour standard system partner for industry, trade, architecture and design. Should be consulted before placing any order.
The colours shown on this catalogue are only a reference and an illustration of the products finishing. The colours shown are not binding because brightness, contrast and colour balance may vary due to the markerial suppliers changes and some differences may occur in tonal range.
Viou and Fabric products are highly susceptible to change its appearance with humidity and temperature. Close attention must be paid to the storage conditions and the acclimatization before, during and after the installation.
Yipcial Indoor Control Standard's state a temperature range of 20°C - 27°C (68°F - 14°F), and a relative thumidity of less than 60%. These would be considered as normal operational levels of JOCAVI[®] products' range.
Despite all the standard sizes of all products, this model can be customised upon previous consultation. Sizes may vary slightly due to their production method and some inherent raw-materials characteristics.

35

TUNED ABSORPTION PANEL

ABSTRACT[®]